

New Products List

• General Applications C0603 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C0603X5R1C224M	C0603	X5R	1C	224	M	0.3
C0603X5R1A224M	C0603	X5R	1A	224	M	0.3
C0603X5R0J224M	C0603	X5R	0J	224	M	0.3

• General Applications C1005 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C1005C0G1H561J	C1005	C0G	1H	561	J	0.5
C1005C0G1H681J	C1005	C0G	1H	681	J	0.5
C1005C0G1H821J	C1005	C0G	1H	821	J	0.5
C1005C0G1H102J	C1005	C0G	1H	102	J	0.5
C1005X7R1H103K/M	C1005	X7R	1H	103	K/M	0.5
C1005X7R1H153K/M	C1005	X7R	1H	153	K/M	0.5
C1005X7R1H223K/M	C1005	X7R	1H	223	K/M	0.5
C1005X7R1H333K/M	C1005	X7R	1H	333	K/M	0.5
C1005X7R1H473K/M	C1005	X7R	1H	473	K/M	0.5
C1005X7R1H683K/M	C1005	X7R	1H	683	K/M	0.5
C1005X7R1H104K/M	C1005	X7R	1H	104	K/M	0.5
C1005X7R1E683K/M	C1005	X7R	1E	683	K/M	0.5
C1005X7R1E104K/M	C1005	X7R	1E	104	K/M	0.5
C1005X7R1C154K/M	C1005	X7R	1C	154	K/M	0.5
C1005X7R1C224K/M	C1005	X7R	1C	224	K/M	0.5
C1005X7R1A224K/M	C1005	X7R	1A	224	K/M	0.5
C1005X5R1H473K/M	C1005	X5R	1H	473	K/M	0.5
C1005X5R1H683K/M	C1005	X5R	1H	683	K/M	0.5
C1005X5R1H104K/M	C1005	X5R	1H	104	K/M	0.5
C1005X5R1E224K/M	C1005	X5R	1E	224	K/M	0.5
C1005X5R1A155K/M	C1005	X5R	1A	155	K/M	0.5
C1005X5R1A225K/M	C1005	X5R	1A	225	K/M	0.5
C1005X5R0J225K	C1005	X5R	0J	225	K	0.5
C1005X5R0J335K/M	C1005	X5R	0J	335	K/M	0.5
C1005X5R0J475K/M	C1005	X5R	0J	475	K/M	0.5
C1005X5R0G225K	C1005	X5R	0G	225	K	0.5
C1005X5R0G335K/M	C1005	X5R	0G	335	K/M	0.5
C1005X5R0G475K/M	C1005	X5R	0G	475	K/M	0.5
C1005X6S1A105K/M	C1005	X6S	1A	105	K/M	0.5
C1005X6S0G225K	C1005	X6S	0G	225	K	0.5

• General Applications C1608 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C1608C0G1H392J	C1608	C0G	1H	392	J	0.8
C1608C0G1H472J	C1608	C0G	1H	472	J	0.8
C1608C0G1H562J	C1608	C0G	1H	562	J	0.8
C1608C0G1H682J	C1608	C0G	1H	682	J	0.8
C1608C0G1H822J	C1608	C0G	1H	822	J	0.8
C1608C0G1H103J	C1608	C0G	1H	103	J	0.8
C1608X7R1H154K/M	C1608	X7R	1H	154	K/M	0.8
C1608X7R1H224K/M	C1608	X7R	1H	224	K/M	0.8
C1608X7R1H334K/M	C1608	X7R	1H	334	K/M	0.8
C1608X7R1H474K/M	C1608	X7R	1H	474	K/M	0.8
C1608X7R1E334K/M	C1608	X7R	1E	334	K/M	0.8
C1608X7R1E474K/M	C1608	X7R	1E	474	K/M	0.8
C1608X7R1E684K/M	C1608	X7R	1E	684	K/M	0.8
C1608X7R1E105K/M	C1608	X7R	1E	105	K/M	0.8
C1608X7R1A225K/M	C1608	X7R	1A	225	K/M	0.8
C1608X7R0J225K/M	C1608	X7R	0J	225	K/M	0.8
C1608X5R1H104K/M	C1608	X5R	1H	104	K/M	0.8
C1608X5R1H154K/M	C1608	X5R	1H	154	K/M	0.8
C1608X5R1H224K/M	C1608	X5R	1H	224	K/M	0.8
C1608X5R1H334K/M	C1608	X5R	1H	334	K/M	0.8
C1608X5R1H474K/M	C1608	X5R	1H	474	K/M	0.8
C1608X5R1H684K/M	C1608	X5R	1H	684	K/M	0.8
C1608X5R1H105K/M	C1608	X5R	1H	105	K/M	0.8
C1608X5R1E155K/M	C1608	X5R	1E	155	K/M	0.8
C1608X5R1E225K/M	C1608	X5R	1E	225	K/M	0.8
C1608X5R1C225K/M	C1608	X5R	1C	225	K/M	0.5
C1608X5R1C335K/M	C1608	X5R	1C	335	K/M	0.8
C1608X5R1C475K/M	C1608	X5R	1C	475	K/M	0.8
C1608X5R1A225K/M	C1608	X5R	1A	225	K/M	0.5
C1608X5R1A475K/M	C1608	X5R	1A	475	K/M	0.5
C1608X5R1A685K/M	C1608	X5R	1A	685	K/M	0.8
C1608X5R1A106K/M	C1608	X5R	1A	106	K/M	0.8
C1608X5R0J475K/M	C1608	X5R	0J	475	K/M	0.5
C1608X5R0J685K/M	C1608	X5R	0J	685	K/M	0.8
C1608X5R0J106K	C1608	X5R	0J	106	K	0.8
C1608X6S1A225K/M	C1608	X6S	1A	225	K/M	0.5
C1608X6S1A475K/M	C1608	X6S	1A	475	K/M	0.8
C1608X6S0G225K/M	C1608	X6S	0G	225	K/M	0.5
C1608X6S0G475K/M	C1608	X6S	0G	475	K/M	0.5
C1608X6S0G475K/M	C1608	X6S	0G	475	K/M	0.8
C1608X6S0G106K/M	C1608	X6S	0G	106	K/M	0.8



New Products List

• General Applications C2012 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C2012C0G1H392J	C2012	C0G	1H	392	J	0.6
C2012C0G1H472J	C2012	C0G	1H	472	J	0.6
C2012C0G1H562J	C2012	C0G	1H	562	J	0.6
C2012C0G1H682J	C2012	C0G	1H	682	J	0.6
C2012C0G1H822J	C2012	C0G	1H	822	J	0.6
C2012C0G1H103J	C2012	C0G	1H	103	J	0.6
C2012C0G1H153J	C2012	C0G	1H	153	J	0.85
C2012C0G1H223J	C2012	C0G	1H	223	J	1.25
C2012C0G1H333J	C2012	C0G	1H	333	J	1.25
C2012X7R1H474K/M	C2012	X7R	1H	474	K/M	1.25
C2012X7R1H684K/M	C2012	X7R	1H	684	K/M	1.25
C2012X7R1H105K/M	C2012	X7R	1H	105	K/M	1.25
C2012X7R1H155K/M	C2012	X7R	1H	155	K/M	1.25
C2012X7R1H225K/M	C2012	X7R	1H	225	K/M	1.25
C2012X7R1E225K/M	C2012	X7R	1E	225	K/M	1.25
C2012X7R1E335K/M	C2012	X7R	1E	335	K/M	1.25
C2012X7R1E475K/M	C2012	X7R	1E	475	K/M	1.25
C2012X7R1C335K/M	C2012	X7R	1C	335	K/M	1.25
C2012X7R1C475K/M	C2012	X7R	1C	475	K/M	1.25
C2012X5R1H105K/M	C2012	X5R	1H	105	K/M	1.25
C2012X5R1H155K/M	C2012	X5R	1H	155	K/M	1.25
C2012X5R1H225K/M	C2012	X5R	1H	225	K/M	1.25
C2012X5R1H335K/M	C2012	X5R	1H	335	K/M	1.25
C2012X5R1H475K/M	C2012	X5R	1H	475	K/M	1.25
C2012X5R1E685K/M	C2012	X5R	1E	685	K/M	1.25
C2012X5R1E106K/M	C2012	X5R	1E	106	K/M	1.25
C2012X5R1C685K/M	C2012	X5R	1C	685	K/M	1.25
C2012X5R1C106K/M	C2012	X5R	1C	106	K/M	0.85
C2012X5R1C226K/M	C2012	X5R	1C	226	K/M	1.25
C2012X5R1A156M	C2012	X5R	1A	156	M	1.25
C2012X5R1A226M	C2012	X5R	1A	226	M	0.85
C2012X5R1A226K/M	C2012	X5R	1A	226	K/M	1.25
C2012X5R0J105K/M	C2012	X5R	0J	105	K/M	0.6
C2012X5R0J105M	C2012	X5R	0J	105	M	0.6
C2012X5R0J156M	C2012	X5R	0J	156	M	0.85
C2012X5R0J226M	C2012	X5R	0J	226	M	0.85
C2012X5R0J336M	C2012	X5R	0J	336	M	1.25
C2012X5R0J476M	C2012	X5R	0J	476	M	1.25
C2012X5R0G476M	C2012	X5R	0G	476	M	1.25
C2012X6S1A106K/M	C2012	X6S	1A	106	K/M	0.85
C2012X6S1A226K/M	C2012	X6S	1A	226	K/M	1.25
C2012X6S0J106K/M	C2012	X6S	0J	106	K/M	0.85
C2012X6S0J226K/M	C2012	X6S	0J	226	K/M	1.25
C2012X6S0G226M	C2012	X6S	0G	226	M	0.85
C2012X6S0G476M	C2012	X6S	0G	476	M	1.25

• General Applications C3216 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C3216C0G1H472J	C3216	C0G	1H	472	J	0.6
C3216C0G1H562J	C3216	C0G	1H	562	J	0.6
C3216C0G1H822J	C3216	C0G	1H	822	J	0.6
C3216C0G1H103J	C3216	C0G	1H	103	J	0.6
C3216C0G1H153J	C3216	C0G	1H	153	J	0.6
C3216C0G1H223J	C3216	C0G	1H	223	J	0.6
C3216C0G1H333J	C3216	C0G	1H	333	J	0.85
C3216C0G1H473J	C3216	C0G	1H	473	J	1.15
C3216C0G1H683J	C3216	C0G	1H	683	J	1.6
C3216C0G1H104J	C3216	C0G	1H	104	J	1.6
C3216X7R1H155K/M	C3216	X7R	1H	155	K/M	1.6
C3216X7R1H225K/M	C3216	X7R	1H	225	K/M	1.6
C3216X7R1H335K/M	C3216	X7R	1H	335	K/M	1.6
C3216X7R1E685K/M	C3216	X7R	1E	685	K/M	1.6
C3216X7R1E106K/M	C3216	X7R	1E	106	K/M	1.6
C3216X5R1H335K/M	C3216	X5R	1H	335	K/M	1.6
C3216X5R1H475K/M	C3216	X5R	1H	475	K/M	1.6
C3216X5R1H685K/M	C3216	X5R	1H	685	K/M	1.6
C3216X5R1H106K/M	C3216	X5R	1H	106	K/M	1.6
C3216X5R1E106K/M	C3216	X5R	1E	106	K/M	1.6
C3216X5R1E226M	C3216	X5R	1E	226	M	1.6
C3216X5R1C226M	C3216	X5R	1C	226	M	1.6
C3216X5R1C336M	C3216	X5R	1C	336	M	1.6
C3216X5R1C476M	C3216	X5R	1C	476	M	1.6
C3216X5R1A226M	C3216	X5R	1A	226	M	1.6
C3216X5R1A336M	C3216	X5R	1A	336	M	1.6
C3216X5R1A476M	C3216	X5R	1A	476	M	1.6
C3216X5R1A107M	C3216	X5R	1A	107	M	1.6
C3216X5R0J107M	C3216	X5R	0J	107	M	1.6
C3216X5R0G107M	C3216	X5R	0G	107	M	1.6
C3216X6S1A476M	C3216	X6S	1A	476	M	1.6
C3216X6S0J476M	C3216	X6S	0J	476	M	1.6
C3216X6S0G107M	C3216	X6S	0G	107	M	1.6

• General Applications C3225 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C3225X7R1H475K/M	C3225	X7R	1H	475	K	2.5
C3225X6S1H475K/M	C3225	X6S	1H	475	K	2.5
C3225X7S1H685K/M	C3225	X7S	1H	685	K	2.5
C3225X5R1H475K/M	C3225	X5R	1H	475	K	2.5
C3225X5R1A336M	C3225	X5R	1A	336	M	2
C3225X5R1A476M	C3225	X5R	1A	476	M	2.5
C3225X6S0J476M	C3225	X6S	0J	476	M	2.5
C3225X6S0J107M	C3225	X6S	0J	107	M	2.5
C3225X6S0G107M	C3225	X6S	0G	107	M	2.5

New Products List

• Flip Type C Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C0510X6S0G224M	C0510	X6S	0G	224	M	0.3
C0510X6S0G474M	C0510	X6S	0G	474	M	0.3
C0816X6S0G474M	C0816	X6S	0G	474	M	0.3
C0816X5R1A474K	C0816	X5R	1A	474	K	0.5

• X7R Mid Voltage C Series


TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C1005X7S2A102K/M	C1005	X7S	2A	102	K	0.5
C1005X7S2A152K/M	C1005	X7S	2A	152	K	0.5
C1005X7S2A222K/M	C1005	X7S	2A	222	K	0.5
C1005X7S2A332K/M	C1005	X7S	2A	332	K	0.5
C1005X7S2A472K/M	C1005	X7S	2A	472	K	0.5
C1005X7S2A682K/M	C1005	X7S	2A	682	K	0.5
C1608X7S2A333K/M	C1608	X7S	2A	333	K	0.8
C1608X7S2A473K/M	C1608	X7S	2A	473	K	0.8
C1608X7S2A683K/M	C1608	X7S	2A	683	K	0.8
C2012X7S2A154K/M	C2012	X7S	2A	154	K	0.85
C2012X7S2A224K/M	C2012	X7S	2A	224	K	0.85
C2012X7S2A334K/M	C2012	X7S	2A	334	K	1.25
C3225X7S2A475K/M	C3225	X7S	2A	475	K	2
C5750X7S2A156M	C5750	X7S	2A	156	M	2.5

• Controlled ESR CER Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
CERD1FX5R0G106M	CERD1F	X5R	0G	106	M	0.85

• Feed Through CKD Series

TDK Part Number	Case Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
CKD61BJB0J105S	CKD61BJB	0J	105	S	0.6
CKD61BJB0J475S	CKD61BJB	0J	475	S	0.6
CKD610JB0J475S	CKD610JB	0J	475	S	0.8
CKD510JB1C474S	CKD510JB	1C	474	S	0.85
CKD510JB1A225S	CKD510JB	1A	225	S	0.85
CKD510JB1A475S	CKD510JB	1A	475	S	0.85
CKD510JB0J106S	CKD510JB	0J	106	S	0.85
CKD510JB0J226S	CKD510JB	0J	226	S	0.85
CKD310JB0J226S	CKD310JB	0J	226	S	1.3



New Products List

• F & G Tight Tolerance C Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C1005C0G1H220F/G	C1005	C0G	1H	220	F/G	0.5
C1005C0G1H470F/G	C1005	C0G	1H	470	F/G	0.5
C1005C0G1H101F/G	C1005	C0G	1H	101	F/G	0.5
C1608C0G1H220F/G	C1608	C0G	1H	220	F/G	0.8
C1608C0G1H470F/G	C1608	C0G	1H	470	F/G	0.8
C1608C0G1H101F/G	C1608	C0G	1H	101	F/G	0.8
C1608C0G1H221F/G	C1608	C0G	1H	221	F/G	0.8
C1608C0G1H471F/G	C1608	C0G	1H	471	F/G	0.8
C1608C0G1H102F/G	C1608	C0G	1H	102	F/G	0.8
C1608C0G2A101F/G	C1608	C0G	2A	101	F/G	0.8
C1608C0G2A102F/G	C1608	C0G	2A	102	F/G	0.8

• General Applications C0402 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C0402C0G1C0R5C	C0402	C0G	1C	0R5	C	0.2
C0402C0G1C010B/C	C0402	C0G	1C	010	B/C	0.2
C0402C0G1C1R1B/C	C0402	C0G	1C	1R1	B/C	0.2
C0402C0G1C1R2B/C	C0402	C0G	1C	1R2	B/C	0.2
C0402C0G1C1R3B/C	C0402	C0G	1C	1R3	B/C	0.2
C0402C0G1C1R5B/C	C0402	C0G	1C	1R5	B/C	0.2
C0402C0G1C1R6B/C	C0402	C0G	1C	1R6	B/C	0.2
C0402C0G1C1R8B/C	C0402	C0G	1C	1R8	B/C	0.2
C0402C0G1C020B/C	C0402	C0G	1C	020	B/C	0.2
C0402C0G1C2R2B/C	C0402	C0G	1C	2R2	B/C	0.2
C0402C0G1C2R4B/C	C0402	C0G	1C	2R4	B/C	0.2
C0402C0G1C2R7B/C	C0402	C0G	1C	2R7	B/C	0.2
C0402C0G1C030B/C	C0402	C0G	1C	030	B/C	0.2
C0402C0G1C3R3B/C	C0402	C0G	1C	3R3	B/C	0.2
C0402C0G1C3R6B/C	C0402	C0G	1C	3R6	B/C	0.2
C0402C0G1C3R9B/C	C0402	C0G	1C	3R9	B/C	0.2
C0402C0G1C040B/C	C0402	C0G	1C	040	B/C	0.2
C0402C0G1C4R3B/C	C0402	C0G	1C	4R3	B/C	0.2
C0402C0G1C4R7B/C	C0402	C0G	1C	4R7	B/C	0.2
C0402C0G1C050B/C	C0402	C0G	1C	050	B/C	0.2
C0402C0G1C5R1B/C/D	C0402	C0G	1C	5R1	B/C/D	0.2
C0402C0G1C5R6B/C/D	C0402	C0G	1C	5R6	B/C/D	0.2
C0402C0G1C060B/C/D	C0402	C0G	1C	060	B/C/D	0.2
C0402C0G1C6R2B/C/D	C0402	C0G	1C	6R2	B/C/D	0.2
C0402C0G1C6R8B/C/D	C0402	C0G	1C	6R8	B/C/D	0.2
C0402C0G1C070B/C/D	C0402	C0G	1C	070	B/C/D	0.2
C0402C0G1C7R5B/C/D	C0402	C0G	1C	7R5	B/C/D	0.2
C0402C0G1C080B/C/D	C0402	C0G	1C	080	B/C/D	0.2
C0402C0G1C8R2B/C/D	C0402	C0G	1C	8R2	B/C/D	0.2
C0402C0G1C090B/C/D	C0402	C0G	1C	090	B/C/D	0.2
C0402C0G1C9R1B/C/D	C0402	C0G	1C	9R1	B/C/D	0.2
C0402C0G1C100E/D	C0402	C0G	1C	100	E/D	0.2
C0402C0G1C110G/J	C0402	C0G	1C	110	G/J	0.2
C0402C0G1C120G/J	C0402	C0G	1C	120	G/J	0.2
C0402C0G1C130G/J	C0402	C0G	1C	130	G/J	0.2
C0402C0G1C150G/J	C0402	C0G	1C	150	G/J	0.2
C0402X5R1C101K	C0402	X5R	1C	101	K	0.2
C0402X5R1C151K	C0402	X5R	1C	151	K	0.2
C0402X5R1C221K	C0402	X5R	1C	221	K	0.2
C0402X5R1C331K	C0402	X5R	1C	331	K	0.2
C0402X5R1C471K	C0402	X5R	1C	471	K	0.2

• General Applications C0402 Series (Con't)

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C0402X5R1C681K	C0402	X5R	1C	681	K	0.2
C0402X5R1A101K	C0402	X5R	1A	101	K	0.2
C0402X5R1A221K	C0402	X5R	1A	221	K	0.2
C0402X5R1A471K	C0402	X5R	1A	471	K	0.2
C0402X7R1A101K	C0402	X7R	1A	101	K	0.2
C0402X7R1A151K	C0402	X7R	1A	151	K	0.2
C0402X7R1A221K	C0402	X7R	1A	221	K	0.2
C0402X7R1A331K	C0402	X7R	1A	331	K	0.2
C0402X7R1A471K	C0402	X7R	1A	471	K	0.2
C0402X7R1A681K	C0402	X7R	1A	681	K	0.2
C0402X5R1A102K	C0402	X5R	1A	102	K	0.2
C0402X5R1A152K	C0402	X5R	1A	152	K	0.2
C0402X5R1A222K	C0402	X5R	1A	222	K	0.2
C0402X5R0J681K	C0402	X5R	0J	681	K	0.2
C0402X5R0J102K	C0402	X5R	0J	102	K	0.2
C0402X5R0J152K	C0402	X5R	0J	152	K	0.2
C0402X5R0J222K	C0402	X5R	0J	222	K	0.2
C0402X5R0J332K	C0402	X5R	0J	332	K	0.2
C0402X5R0J472K	C0402	X5R	0J	472	K	0.2
C0402X5R0J682K	C0402	X5R	0J	682	K	0.2
C0402X5R0J103K	C0402	X5R	0J	103	K	0.2

• High Q C0603 Series

TDK Part Number	Case Code	T.C. Code	Voltage Code	Capacitance Code	Tol. Code	Thickness
C0603C0G1E0R2B	C0603	C0G	1E	0R2	B	0.3
C0603C0G1E0R3B	C0603	C0G	1E	0R3	B	0.3
C0603C0G1E0R4B	C0603	C0G	1E	0R4	B	0.3
C0603C0G1E0R5B	C0603	C0G	1E	0R5	B	0.3
C0603C0G1E0R6B	C0603	C0G	1E	0R6	B	0.3
C0603C0G1E0R7B	C0603	C0G	1E	0R7	B	0.3
C0603C0G1E0R8B	C0603	C0G	1E	0R8	B	0.3
C0603C0G1E0R9B	C0603	C0G	1E	0R9	B	0.3
C0603C0G1E010B/C	C0603	C0G	1E	010	B	0.3
C0603C0G1E1R2B/C	C0603	C0G	1E	1R2	B	0.3
C0603C0G1E1R5B/C	C0603	C0G	1E	1R5	B	0.3
C0603C0G1E1R8B/C	C0603	C0G	1E	1R8	B	0.3
C0603C0G1E020B/C	C0603	C0G	1E	020	B	0.3
C0603C0G1E2R2B/C	C0603	C0G	1E	2R2	B	0.3
C0603C0G1E2R7B/C	C0603	C0G	1E	2R7	B	0.3
C0603C0G1E030B/C	C0603	C0G	1E	030	B	0.3
C0603C0G1E3R3B/C	C0603	C0G	1E	3R3	B	0.3
C0603C0G1E3R9B/C	C0603	C0G	1E	3R9	B	0.3
C0603C0G1E040B/C	C0603	C0G	1E	040	B	0.3
C0603C0G1E4R7B/C	C0603	C0G	1E	4R7	B	0.3
C0603C0G1E050B/C	C0603	C0G	1E	050	B	0.3
C0603C0G1E5R6B/C	C0603	C0G	1E	5R6	B	0.3
C0603C0G1E060B/C	C0603	C0G	1E	060	B	0.3
C0603C0G1E6R8B/C	C0603	C0G	1E	6R8	B	0.3
C0603C0G1E070B/C	C0603	C0G	1E	070	B	0.3
C0603C0G1E080B/C	C0603	C0G	1E	080	B/C	0.3
C0603C0G1E8R2B/C	C0603	C0G	1E	8R2	B/C	0.3
C0603C0G1E090B/C	C0603	C0G	1E	090	B/C	0.3
C0603C0G1E100E/D	C0603	C0G	1E	100	E/D	0.3
C0603C0G1E120G/J	C0603	C0G	1E	120	G/J	0.3
C0603C0G1E150G/J	C0603	C0G	1E	150	G/J	0.3

